



Category (ETIM):	Variable device mount
Type:	Device mount IP20-SDGVLB LED
Order number:	18314604150
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
System performance (W):	73
Luminaire luminous flux (lm):	10000
lm/W:	146
Ambient temperatures:	10°C / 35°C
Certifications:	IP 20, protection class I, F, DIN10500/Food, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	2.1
Dimensions LxWxH/DxH (mm):	1531 x 63 x 46
mounting method:	Mounting rail system mounting
EAN-number:	4020863336326
Commodity code:	94051098


SDGVLB LED 10000lm 840 • vw • ED • 18314604150



Lighting technology
Linear.Lens.Profil-direct wide distribution
SDGVLB LED 10000 lm 840



ηLB	100 %
lm/W	146
Φ ↓/↑	99 % / 1 %
UGR q/l	24.9 / 29.1



Quick-fit mounting system Variable device mount; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated lateral lever locks. LED unit in housing length for optically seamless light run. Can be variably positioned on the mounting rail. Housing colour traffic white RAL 9016; Direct, wide light distribution using Linear.Lens.Profil made of matt PMMA plastic. Optically seamless light run. Heat-resistant cables including connection cable 1 m and rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxH/DxH (mm): 1531 x 63 x 46
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 10000
lm/W: 146
Operating device: Electronic driver (1 pcs.)
System performance (W): 73
Conditions: Suitable for use in ambient temperatures of 10°C to 35°C
Certifications: IP 20, protection class I, F, DIN10500/Food, Indoor, CE

Regiolux GmbH
Type: SDGVLB LED 10000 840 ET vw
Article number: 18314604150
Product deep link: <http://www.regiolux.de/de/article/18314604150>
5 year guarantee after registration on website.