

## Cutting body solid carbide TiAlN for Top Drill M 1

For universal use up to 1300 N/mm<sup>2</sup>



### Application:

High-performance drilling in conjunction with indexable insert drill for universal application up to 1300 N/mm<sup>2</sup>

### Execution:

- Precision-ground indexable insert, tip angle 140°

### Advantage:

- Simply replacement of cutting body: No screws or clamps required
- The cutting body can be replaced using a wrench, which is supplied with each tool body
- No regrinding costs
- Consistent performance from cutting edge to cutting edge



<b>Art. no.</b>	<b>11224 120</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	3849071
<b>Cutting material</b>	SC
<b>Carbide type</b>	WU25PD
<b>Cutting edge diameter</b>	12 mm
<b>Indexable insert type</b>	W18
<b>Surface</b>	TiAlN
<b>Cutting direction</b>	Right-hand cutting
<b>Angle of the tip</b>	140 Degree
<b>Gross Weight</b>	0.007 kg
<b>Product Group</b>	1XA

### EAN

4021169584596