

SSRC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application

For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17830 823
ISO name	SCRC R/L 2020 K12
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	24 mm
Programming size	22 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Left

EAN-Code

4050293562750