

Half-pallet trolley zinc-plated, height-adjustable

Corner braces, 800 x 600 mm, load-bearing capacity 800 kg



Application:

Ideal for the transport of Euro half pallets, Euroboxes and crates

Execution:

- High-quality and long-lasting zinc plating
- Height adjustment range: 655-835 mm

Advantage:

- Supports more efficient material transport
- Ergonomics - height-adjustable



| | |
|------------------------------------|--------------------------|
| Art. no. | 50291 214 |
| Brand | KONGAMEK |
| Manufacturer Part Number | KM222-EPHB |
| Type | Height-adjustable |
| Load-carrying capacity | 800 kg |
| Length | 846 mm |
| Width | 646 mm |
| Height | 704 mm |
| Loading surface length | 800 mm |
| Loading-surface width | 600 mm |
| Material | Steel / steel |
| Material of loading surface | Steel frame |
| Colour | Silver coloured |
| Surface | Zinc plated |
| Number of steering rollers | 2 |
| Number of fixed rollers | 2 |
| With wheel lock | Yes |
| ESD-capable | No |
| Adjustable in height | Yes |
| Min. height adjustment | 655 mm |
| Max. height adjustment | 830 mm |
| Min./max. height adjustment | 655-830mm |
| Wheel diameter | 200 mm |
| Material of wheel | Solid rubber |
| Suitable for transporting | Euro boxes, Boxes, Boxes |
| Gross Weight | 32.610 kg |
| Product Group | 5AT |

EAN

7350112292965