

Tool cabinet with shelves

Doors optionally with perforated panel, slotted panel or viewing window

[®]RasterPlan

Application:

For secure and clearly-arranged storage of high-quality tools.

Version:

- Welded sheet steel frame with perforated rear wall throughout with 10 x 10 mm perforation grid, for attaching support elements
- Overlay double-walled, twist-resistant hinged doors, opening angle over 200°
- Doors lockable with bascule lock engaging on 3 sides

Art. no.	50639 224
Door design	Slotted plates
Width	1000 mm
Depth	410 mm
Height	1600 mm
Number of shelves	1 PCS
Shelf width	1000 mm
Shelf depth	410 mm
Load-carrying capacity per shelf	80 kg
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Surface	Lacquered
Cabinet colour	Light grey RAL 7035



EAN-Code

4251142237496