

## Aluminium extension ladder with rungs, 420 mm wide, nivello(R) stabiliser

Lean-on version, 2 pieces



### Application:

Ideal for particularly high heights.

### Execution:

- Stable rectangular tube side-rails
- Square rungs 30 x 30 mm, grooved on both sides
- 4x flanged rung/side-rail connection
- Easy height adjustment thanks to the insertion hook with automatically engaging lift-off protection
- Upper ladder from size 2x14 rungs with wall castors
- Corrosion-resistant guide fittings
- Upper ladder up to 3.0 m with nivello® ladder shoes
- Rung spacing: 280 mm
- Ladder width: 420 mm (without stabiliser)
- Standard stabiliser with non-slip ladder shoes

### Advantage:

- nivello® ladder shoes - work angle verification and replaceable foot plates

### Delivery:

The stabiliser is enclosed separately and is screwed to the lower end of the side-rail with two screws.



<b>Art. no.</b>	<b>59002 228</b>
<b>Brand</b>	MUNK GUENZBURGER STEIGTECHNIK
<b>Manufacturer Part Number</b>	20412
<b>Working height</b>	7.2 m
<b>Number of rungs</b>	2 x 12
<b>Length (extended)</b>	6.04 m
<b>Length (pushed together)</b>	3.62 m
<b>Weight</b>	15.2 kg
<b>Length stabiliser bar</b>	1.2 m
<b>Rail height</b>	0.073 m
<b>Max. load capacity</b>	150 kg
<b>Material</b>	Aluminium
<b>Type</b>	nivello stabiliser, 2 pieces
<b>Accessibility</b>	One-sided
<b>Anodised</b>	No
<b>Rung depth</b>	30 mm
<b>Width (bottom)</b>	0.42 m
<b>ESD-capable</b>	No
<b>Transport width</b>	0.425 m
<b>Transport length</b>	3.601 m
<b>Transport depth</b>	0.15 m
<b>Gross Weight</b>	18.500 kg
<b>Product Group</b>	5AP

### EAN

4031405204126