



Datenblatt - Fiche technique - Data sheet


**11.02.8803**



ROLINE GOLD USB 2.0 Kabel, Typ A-B, 3,0m

ROLINE GOLD Câble USB 2.0, type A-B, 3,0m

ROLINE GOLD USB 2.0 Cable, A - B, M/M, 3.0 m




### Pin Out

| P1    |            | P2    |
|-------|------------|-------|
| 1     | Red        | 1     |
| 2     | White      | 2     |
| 3     | Green      | 3     |
| 4     | Black      | 4     |
| Shell | Drain Wire | Shell |

1. Cable UL2725 28AWG(7/0.127TC)\*1P+24AWG(7/0.2TC)\*2C+AEB(65%AL)  
Jacket: Black Color with Braid, OD=4.5mm
2. Conn USB Type A M, Insulator: White, Pin Gold Plated 3u"  
Shell: Gold Plated
3. Conn USB Type B M, Insulator: White, Pin Gold Plated 3u"  
Shell: Gold Plated
4. Molding 45P, Color Black
5. Hood USB Type A M with USB 2.0 Mark(Laser), Aluminum, Color: Gold
6. Hood USB Type B M with USB 2.0 Mark(Laser), Aluminum, Color: Gold

| P. / N.    | Length                                 |
|------------|--|
| 11.02.8802 | 1800 <sup>+50</sup> / <sub>-0</sub> mm |
| 11.02.8803 | 3000 <sup>+60</sup> / <sub>-0</sub> mm |
| 11.02.8805 | 4500 <sup>+60</sup> / <sub>-0</sub> mm |

| REV. | DATE | CONTENTS OF CHANGE | DESIGNER | TOL ±   |     |     |     |     |     |     |     | APPROVAL | CHECK | DRAWING | DESIGN | DRAWING NAME | ROLINE USB 2.0 AM to BM Cable   |   |  |     |
|------|------|--------------------|----------|---------|-----|-----|-----|-----|-----|-----|-----|----------|-------|---------|--------|--------------|---|---|--|-----|
|      |      |                    |          | RANGE   | Plc | Met | Ins | Por | v   | Cab | Pac |          |       |         |        |              |   |   |  | Gas |
| ①    |      |                    |          | 0~6     | 0.1 | 0.1 | 0.1 | 0.2 | 0.5 | 1   | 0.5 | 0.2      | Allen | Allen   |        | Allen        | DATE  | PART NO. 11.02.8802 / 11.02.8803 / 11.02.8805 |  |     |
| ②    |      |                    |          | 6~30    | 0.1 | 0.1 | .15 | .25 | 1   | 1   | 0.5 | .25      |       |         |        |              | 2016-05-6   | ROO   |  |     |
| ③    |      |                    |          | 30~80   | 0.1 | .15 | 0.2 | 0.3 | 2   | 1.5 | 1   | 0.3      |       |         |        |              |   |   |  |     |
| ④    |      |                    |          | 80~180  | .15 | .15 | .25 | 0.3 | 2   | 2   | 1   | .45      |       |         |        |              |   |   |  |     |
| ⑤    |      |                    |          | 180~315 | .15 | 0.2 | 0.3 | 0.4 | 2.5 | 2   | 1   | 0.6      |       |         |        |              |   |   |  |     |
|      |      |                    |          | 315~800 | 0.2 | 0.3 | 0.4 | 0.5 | 3   | 3   | 2   | 1.1      | SCALE | 1:1     | UNIT   | MM           |  |   |  |     |