

# PC 1919 13 T

**FIBOX**  
Enclosing innovations



Sample image

**Order symbol:** PC 1919 13 T

**Product nbr:** 5330059

UL Code: 5320059

UL Name: UL PC 1919 13 T

**Description:** Enclosure. PC


**Remarks:** Transparent cover

**Including:** Base with screws for mounting plate. cover with PUR gasket and polyamide cover screws.

**EAN:** 6418074005397

**El. number:**

- Finland: 3423801
- Denmark:
- Sweden: 2539436



**Dimensions:** Height Width Depth

mm: 190 190 130

**Accessories:**

EKHVT Base Panel for enclosures

mm:	190	190	190
inch:	7.48	7.48	5.12

#### Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Clear transparent
Gasket material:	Polyurethane

#### Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

EKV 12	DIN-35 Mounting rail, for enclosures: (148 x 148 x 1)
--------	--

#### Rating:

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5*
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

#### Certificates:

Certificate NCS FI 30308