

Słupy dystansowe

Opis artykułu/ilustracje produktu



Opis


Materiał:

Stal.

Wersja:

ocynkowane i pasywowane na niebiesko.

Rysunki



Przegląd artykułów

Słupy dystansowe

Nr Zamówienia	D1	E	L	SW	T
K1302.205025	M5	9,2	25	8	8
K1302.205030	M5	9,2	30	8	8
K1302.205035	M5	9,2	35	8	8
K1302.206030	M6	11,5	30	10	9
K1302.206035	M6	11,5	35	10	9
K1302.206040	M6	11,5	40	10	9
K1302.206050	M6	11,5	50	10	9
K1302.206060	M6	11,5	60	10	9
K1302.208030	M8	15	30	13	12
K1302.208035	M8	15	35	13	12
K1302.208040	M8	15	40	13	12
K1302.208050	M8	15	50	13	12
K1302.208060	M8	15	60	13	12
K1302.208090	M8	15	90	13	12
K1302.210040	M10	18,5	40	16	15
K1302.210045	M10	18,5	45	16	15
K1302.210055	M10	18,5	55	16	15
K1302.210065	M10	18,5	65	16	15
K1302.210095	M10	18,5	95	16	15
K1302.210115	M10	18,5	115	16	15
K1302.212040	M12	20,8	40	18	18
K1302.212045	M12	20,8	45	18	18
K1302.212055	M12	20,8	55	18	18
K1302.212065	M12	20,8	65	18	18
K1302.212095	M12	20,8	95	18	18
K1302.212115	M12	20,8	115	18	18

