

## Bauart 1

Ständer													
Höhe mm	2500				3000				3500				
Tiefe mm	600	800	1000	1200	600	800	1000	1200	600	800	1000	1200	
<b>einseitig</b>	Traglast kg	3030	2490	2040	1680	2520	2120	1800	1560	2100	1750	1500	1300
		190653	190664	190675	190686	190697	190711	190722	190733	190744	190755	190766	190777
		---	---	---	---	---	---	---	---	---	---	---	---
<b>beidseitig</b>	Traglast kg	6060	4980	4080	3360	5040	4240	3600	3120	4200	3500	3000	2600
		190788	190799	190802	190813	190824	190835	190846	190857	190868	190879	190904	190915
		---	---	---	---	---	---	---	---	---	---	---	---

  

Kragarme					Diagonalverband				
Tiefe mm	600	800	1000	1200	Breite mm	1000	1250	1500	2000
Traglast kg	860	640	510	410	Höhe mm	189166	189177	189188	189199
Stück	190926	191612	191623	191634	2500	---	---	---	---
	---	---	---	---	Höhe mm	189202	189213	189224	189235
					3000	---	---	---	---
					Höhe mm	190595	190609	190631	190642
					3500	---	---	---	---

  

Längsverbinder					Abrollssicherung
Breite mm	1000	1250	1500	2000	Höhe 100 mm
VE =	191645	191656	191667	191678	191689
2 Stück	---	---	---	---	---

## Bauart 2

Ständer													
Höhe mm	2500				3000				3500				
Tiefe mm	600	800	1000	1200	600	800	1000	1200	600	800	1000	1200	
<b>einseitig</b>	Traglast kg	5450	4400	3660	3120	4800	4020	3440	3010	4080	3480	3000	2640
		191995	192003	192014	192091	192105	192171	192182	192604	192615	192626	192637	192648
		---	---	---	---	---	---	---	---	---	---	---	---
<b>beidseitig</b>	Traglast kg	10900	8800	7320	6240	9600	8040	6880	6020	8160	6960	6000	5280
		192728	192794	192808	192819	192841	192852	192863	192874	192885	192896	193254	193265
		---	---	---	---	---	---	---	---	---	---	---	---

  

Kragarme					Diagonalverband				
Tiefe mm	600	800	1000	1200	Breite mm	1000	1250	1500	2000
Traglast kg	950	710	560	460	Höhe mm	191703	191714	191725	191838
Stück	193276	193287	193298	193301	2500	---	---	---	---
	---	---	---	---	Höhe mm	191849	191871	191882	191893
					3000	---	---	---	---
					Höhe mm	191907	191918	191929	191984
					3500	---	---	---	---

  

Längsverbinder					Abrollssicherung
Breite mm	1000	1250	1500	2000	Höhe 100 mm
VE =	193312	193323	193334	193345	193367
2 Stück	---	---	---	---	---

## Bauart 3

Ständer																
Höhe mm	3000					3500					4000					
Tiefe mm	800	1000	1200	1500	1850	800	1000	1200	1500	1850	800	1000	1200	1500	1850	
<b>einseitig</b>	Traglast kg	7000	5880	5040	4140	3060	6300	5460	4860	4140	3000	5520	4860	4260	3660	2760
		194097	194111	194122	194133	194144	194155	194177	194188	194304	194315	194326	194381	194392	194406	194417
		---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
<b>beidseitig</b>	Traglast kg	14000	11760	10080	8280	6120	12600	10920	9720	8280	6000	11040	9720	8520	7320	5520
		194428	194596	194621	194632	194643	194654	194665	194676	194687	194712	194723	194734	700035	700046	700057
		---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

  

Kragarme						Diagonalverband					
Tiefe mm	800	1000	1200	1500	1850*	Breite mm	900	1000	1250	1500	2000
Traglast kg	1230	980	810	640	450	Höhe mm	193378	193389	193403	193414	193425
Stück	700068	700079	700104	700115	700126	3000	---	---	---	---	---
	---	---	---	---	---	Höhe mm	193436	193447	193458	193469	193491
						3500	---	---	---	---	---
						Höhe mm	193505	193516	193527	193538	193549
						4000	---	---	---	---	---

  

\*Nutzlänge für Spanplatte 2100 mm

Längsverbinder						Abrollssicherung
Breite mm	900	1000	1250	1500	2000	Höhe 100 mm
VE =	700137	700148	700159	700181	700192	700206
2 Stück	---	---	---	---	---	---

  

\*Nutzlänge für Spanplatte 2100 mm

## Bauart 4

Ständer																
Höhe mm	3500					4000					4500					
Tiefe mm	800	1000	1200	1500	1850	800	1000	1200	1500	1850	800	1000	1200	1500	1850	
<b>einseitig</b>	Traglast kg	8520	7440	6540	5400	4020	7620	6660	5940	5100	3900	6700	5900	5300	4150	2750
		700421	700432	700443	700454	700465	700476	700487	700498	700501	700512	700523	700534	700545	700556	700567
		---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
<b>beidseitig</b>	Traglast kg	17040	14880	13080	10800	8040	15240	13320	11880	10200	7800	13400	11800	10600	8300	5500
		700578	700589	700603	700614	700625	700636	700647	700658	700669	700691	700705	700716	700727	700738	700749
		---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

  

Kragarme						Diagonalverband					
Tiefe mm	800	1000	1200	1500	1850*	Breite mm	900	1000	1250	1500	2000
Traglast kg	1800	1430	1190	950	660	Höhe mm	700217	700228	700239	700261	700272
Stück	700771	700782	700793	700807	700818	3500	---	---	---	---	---
	---	---	---	---	---	Höhe mm	700283	700294	700308	700319	700341
						4000	---	---	---	---	---
						Höhe mm	700352	700363	700374	700385	700396
						4500	---	---	---	---	---

  

\*Nutzlänge für Spanplatte 2100 mm

Längsverbinder						Abrollssicherung
Breite mm	900	1000	1250	1500	2000	Höhe 100 mm
VE =	700829	700851	700862	700873	700884	700895
2 Stück	---	---	---	---	---	---