

General Information

Extended Product Type:	232BS6
Product ID:	2CMA193314R1000
EAN:	7392696933148
Catalog Description:	Surface inlet, 6h, 32A, IP44, 2P+E
Long Description:	Surface Inlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Inlets

Ordering

EAN:	7392696933148
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	94 mm
Product Net Height:	85 mm
Product Net Length:	153 mm
Product Net Depth:	153 mm
Product Net Weight:	0.44 kg

Container Information

Package Level 1 Width:	179 mm
Package Level 1 Length:	430 mm
Package Level 1 Height:	193 mm
Package Level 1 Gross Weight:	0.27 kg
Package Level 1 EAN:	7392696933148
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Surface inlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232BS6
Number of Poles:	2
Object Classification Code:	2CMT005069
Product Main Type:	EBS
Product Name:	Industrial Surface Inlet
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	200 ... 250 V 200 ⚡ 250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Surface Inlets
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2417180

UNSPSC: 39120000

