

SylFire - Mains Voltage (GU10 - no lamp)

SYLFIRE BAS TILT CHR GU10 1P
0059740



Product features

- SYLFIRE BAS TILT CHR GU10 1P



PRODUCT OVERVIEW

Product name	SYLFIRE BAS TILT CHR GU10 1P
Technology	Halogen
Cap/Base	GU10
Housing	Stainless steel
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
Warranty	5 years
Light source included	Fixture without Lightsource
Housing colour	Chrome
IP rating	IP65/20
Product EAN number	5410288597409

DATA TABLE

General data

Product name	SYLFIRE BAS TILT CHR GU10 1P
Technology	Halogen
Cap/Base	GU10
Housing	Stainless steel
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
Warranty	5 years

Optical data

Adjustable chromaticity	N
-------------------------	---

Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V

SylFire - Mains Voltage (GU10 - no lamp) SYLFIRE BAS TILT CHR GU10 1P 0059740

Nominal Frequency (Hz)	50/60Hz
------------------------	---------

Physical data

Housing colour	Chrome
IP rating	IP65/20
Nominal Product Height (mm)	98
Cutout Dimensions (W x L in mm or Diameter in mm)	86
Max. Lamp Diameter (mm) - D	92
Weight (kg)	0.301

Packaging

Single packaging type	Carton
Product EAN number	5410288597409
Packaging single length / height (cm)	15.0
Packaging single width (cm)	10.47
Packaging single depth (cm)	10.93
DUN14 (outer)	15410288597406
Units per outer package	20
Packaging outer length / height (cm)	55.4
Packaging outer width (cm)	33.5
Packaging outer depth (cm)	25.1

TECHNICAL DRAWINGS

