

## Angular milling cutter 90°

For indexable milling inserts LN.X 1510..

**ATORN®**

### Application


4 flutes per indexable milling insert and special chip shape geometry for profitability and high cutting rates when milling faces, milling corners, trimming and milling grooves.

### Version

- Wear-resistant, nickel-plated version
- With internal cooling

### Advantage

- 4 cutting edges on one double-sided indexable insert
- Special chip shape geometry for low power consumption
- Thick inserts



<b>Art. No.</b>	<b>16016 450</b>
<b>Cutting edge diameter</b>	50 mm
<b>Length</b>	40 mm
<b>Bore diameter</b>	22 mm
<b>max. ap</b>	14 mm
<b>Number of cutting edges</b>	5 PCS
<b>Suitable indexable insert no.</b>	2

### EAN-Code

4050293344462