

## Clamping heads, round version

**ORION®**

### Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

### Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

<b>Art. no.</b>	<b>22001 038</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22001038
<b>Size</b>	32
<b>Design</b>	Without stem
<b>Profile shape</b>	Round with linear- and transverse grooves
<b>Clamping diameter</b>	15 mm
<b>Length</b>	44 mm
<b>Min./max. clamping range diameter</b>	11-32 mm
<b>Gross Weight</b>	0.440 kg
<b>Product Group</b>	2AO



### EAN

4053625466542