

## Wheeled workbench, working height 790 mm

With 4 drawers and 1 shelf

### Application:

The mobile workstation with versatile options for use.

### Execution:

- Solidly welded sheet steel structure with end-to-end closed rear wall
- Push handlebar on one front side
- Workbench top panel made of solid beech, glued together longitudinally in bars, thickness 40 mm
- Optionally with integrated housing on the side, fitted with easy-view tilting bins



<b>Art. no.</b>	<b>50272 075</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50272075
<b>Number of fixed rollers</b>	2 PCS
<b>Working height</b>	790 mm
<b>Number of steering rollers</b>	2 PCS
<b>Worktop width</b>	1140 mm
<b>Number of drawers</b>	4 PCS
<b>Worktop height</b>	40 mm
<b>Number of doors</b>	1 PCS
<b>Worktop depth</b>	650 mm
<b>Pullout type</b>	Partial extension
<b>On castors</b>	Yes
<b>Moving device, can be lowered</b>	No
<b>Colour of front</b>	Optional
<b>Cabinet colour</b>	Optional
<b>With single pull-out safety brake</b>	No
<b>Surface</b>	Powder-coated
<b>With wheel lock</b>	Yes
<b>Load-carrying capacity</b>	600 kg
<b>Dynamic load-carrying capacity</b>	400 kg
<b>Wheel diameter</b>	125 mm
<b>Type</b>	mobile
<b>Lock type</b>	Cylinder lock
<b>Material of worktop</b>	Solid beech
<b>Drawer front height</b>	2 x 90 mm, 1 x 150 mm, 1 x 210 mm
<b>Material</b>	Sheet steel
<b>Drawer width (inner dimension)</b>	410 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	410 x 540 mm
<b>Drawer depth (inner dimension)</b>	540 mm
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Material of wheel</b>	Polyurethane
<b>Central locking</b>	Yes
<b>Gross Weight</b>	127.000 kg
<b>Product Group</b>	501

### EAN

4039247902323