

Blind riveter

RRI-PR series



Execution:

- Industrial pneumatic-hydraulic blind riveter with container.
- Very fast and powerful, with a low air consumption per riveting operation.
- Lightweight and ergonomically designed for optimal working comfort.
- Available with multiple nose pieces for different capacities.



Art. no.	75066 392
Brand	RED ROOSTER
Manufacturer Part Number	RRI-PR40948
Connection thread	NPT 1/4 inch
Suitable for max. rivet diameter	4.8 mm
Stroke length	22 mm
Included in delivery	Wrench, oiler, rubber base and 4 and 4.8 mm nose pieces
Air consumption per impact	1.2 l
Weight of machine	1.9 kg
Model	RRI-PR40948
Inner hose diameter	9.5 mm
Max. tensile force	9200 N
Vibration	1 m/s ²
Gross Weight	2.470 kg
Product Group	7AE

EAN

8717981364725