

Miniature brushes round/cup/wire end brushes

Shank-Ø 2.34 mm and 3 mm

ATORN[®]

Application

For cleaning and polishing as well as for light deburring work in holes and cavities. Due to the low trim width, targeted processing is possible in hard-to-reach spots.

Art. no.	76086 131
Type	Cylinder wire brush
Edging material	Natural bristle goat hair
Max. rotation speed	25000 rpm
Number of pieces per packet	12

EAN-Code

4050293449334

