

TorqueFix® and Torque cable key.


2850 TorqueFix® torque screwdriver.
 With a fixed torque value pre-set by Wiha.
Automatic release.

- Handle:** Ergonomic multi-component handle, particularly light and compact. Handle sizes proportioned to optimise torque setting. Audible and perceptible click when the pre-set torque has been attained.
- Standards:** EN ISO 6798, BS EN 26789, ASME B107.14M.
- Accuracy:** ±6%, traceable to national standards.
- Application:** For applications where recommended torque settings are important. Use in combination with a Wiha torque interchangeable blade.
- Extra:** Delivered in practical plastic box, incl. factory calibration certificate.
- Note:** The below articles are available from stock. Further articles with pre-set, customer torque values of between 0.15 and 8 Nm are available on request. Bit holders or blades are not included in delivery.
- Individual:** Products can be designed individually using the configurator at mytorque.wiha.com. (Can be chosen freely: text field, torque unit, torque value)

| Order-No. | Nm | ±% | ⊙ | ↔ | ↕ | ↔ |
|-----------|-----|----|---|-----|----|---|
| 26925 | 0.4 | 6% | 4 | 112 | 23 | 1 |
| 26127 | 0.5 | 6% | 4 | 112 | 23 | 1 |
| 26047 | 0.6 | 6% | 4 | 112 | 23 | 1 |
| 26327 | 0.8 | 6% | 4 | 112 | 23 | 1 |
| 26048 | 0.9 | 6% | 4 | 112 | 23 | 1 |
| 26133 | 1.1 | 6% | 4 | 119 | 30 | 1 |
| 26049 | 1.2 | 6% | 4 | 119 | 30 | 1 |
| 26901 | 1.5 | 6% | 4 | 119 | 30 | 1 |
| 26051 | 2.0 | 6% | 4 | 119 | 30 | 1 |
| 26128 | 2.5 | 6% | 4 | 119 | 30 | 1 |
| 26052 | 3.0 | 6% | 4 | 126 | 36 | 1 |
| 26129 | 3.8 | 6% | 4 | 126 | 36 | 1 |
| 26053 | 5.0 | 6% | 4 | 132 | 41 | 1 |
| 26130 | 5.5 | 6% | 4 | 132 | 41 | 1 |
| 34533 | 6.0 | 6% | 4 | 132 | 41 | 1 |
| 26131 | 7.2 | 6% | 4 | 132 | 41 | 1 |

easyTorque.


292 easyTorque torque screwdriver.
 With a fixed torque value ex-factory.

- Handle:** Multi-component handle optimally designed for the hand enables optimal power transmission. Audible and perceptible click when the pre-set torque has been attained. Rapid identification with imprint on handle end. Unlimited loosening torque. Mechanism insensitive to industrial lubricants. Compatible with all blades of the 2859 series.
- Accuracy:** ±10%
- Application:** For applications where recommended torque settings are important. Use in combination with a Wiha torque interchangeable blade.
- Note:** Bit holders or blades are not included in delivery.

| Order-No. | Nm | ±% | ⊙ | ↔ | ↕ | ↔ |
|-----------|-----|-----|---|-----|----|---|
| 36229 | 0.5 | 10% | 4 | 130 | 34 | 1 |
| 36230 | 0.6 | 10% | 4 | 130 | 34 | 1 |
| 36240 | 0.9 | 10% | 4 | 130 | 34 | 1 |
| 36231 | 1.1 | 10% | 4 | 130 | 34 | 1 |
| 36233 | 1.2 | 10% | 4 | 130 | 34 | 1 |
| 36234 | 1.4 | 10% | 4 | 130 | 34 | 1 |
| 36235 | 2.0 | 10% | 4 | 130 | 34 | 1 |
| 36236 | 2.5 | 10% | 4 | 130 | 34 | 1 |
| 36237 | 3.0 | 10% | 4 | 130 | 34 | 1 |
| 36238 | 3.8 | 10% | 4 | 130 | 34 | 1 |
| 36320 | 4.0 | 10% | 4 | 130 | 34 | 1 |
| 36321 | 4.5 | 10% | 4 | 130 | 34 | 1 |
| 36239 | 5.0 | 10% | 4 | 130 | 34 | 1 |


2850 S2 Torque cable key set for circular plug connectors.
 For Wiha torque screwdrivers.

- Handle:** TorqueFix® torque screwdrivers. Ergonomic multi-component handle, particularly light and compact.
- Material:** Robust, glass-fibre reinforced plastic combines the high quality hexagonal stainless steel insert with the blade tang of chrome-vanadium-molybdenum steel.
- Application:** For controlled fastening of circular plug connectors with hexagonal head according to specified torque.

| Order-No. | Nm | ⊙ | mm | ↔ | ↕ | ↔ |
|-----------|-----|----|-----|----|-----|----|
| 36846 | 0.4 | 9 | 230 | 78 | 112 | 23 |
| 36847 | 0.6 | 13 | 230 | 78 | 112 | 23 |
| 36848 | 1.5 | 22 | 240 | 90 | 119 | 30 |