



▶ 1PK-054S Flat Nose Plier




Material	HRC		OAL. (mm)
	Body	Cutting edge	
S45C	43'±3'		135

▶ 1PK-055S Bent Nose Plier




Material	HRC		OAL. (mm)
	Body	Cutting edge	
S45C	43'±3'		130

▶ 1PK-046S Needle Nose Plier



Material	HRC		OAL. (mm)
	Body	Cutting edge	
S45C	43'±3'		150

▶ 1PK-036S Long Nose Plier




Material	HRC		Application			OAL. (mm)
	Body	Cutting edge	Hard steel	Copper		
S45C	43'±3'	48'±3'	Ø 0.8mm	Ø 1.6mm		136

Non-Slip Handles Precision Pliers




- Clean and smooth cutting
- Lightweight design for easy operation
- Particularly design for electronic and precision field



Individual packing: Blister card

▶ 1PK-037S Diagonal Cutting Plier



Material	HRC		Application			OAL. (mm)
	Body	Cutting edge	Hard steel	Soft steel	Copper	
S45C	43'±3'	48'±3'	Ø 0.8mm	Ø 1.3mm	Ø 1.6mm	110


▶ PM-808 Plastic Cutting Plier



- Precision design for cutting and assembly electronics, craft, mold and more. Tapered and relieved head, more thin and slim allows reaching to hard to reach area.



Special for Ø 0.3-1.3mm



Material	Body	Handle	HRC		Application	OAL. (mm)
			Body	Cutting edge		
S60C	PVC		45'±2'	59'±2'	Ø 0.3-1.3mm	117



Tapered and relieved head super slim.