



SIMATIC S7-1500, Front connector in push-in design, 40-pole for 25 mm wide modules and compact CPUs of the S7-1500, incl. cable tie

General information	
Product type designation	Front connector
connection method / header	
Connection I/O signals	
<ul style="list-style-type: none"> • Connection method • Number of lines per connection 	Push-in terminal 1; or max. 8x 2 conductors to 1.5 mm ² (in total) in a shared end sleeve and max. 32x 0.75 mm ² single core
Conductor cross-section in mm ²	
— Connectable cable cross-sections for massive cables, min.	0.25 mm ²
— Connectable cable cross-sections for massive cables, max.	1.5 mm ² ; max. 32x 0.75 mm ² , 8x 1.5 mm ²
— Connectable cable cross-sections for flexible cables without end sleeve, min.	0.25 mm ²
— Connectable cable cross-sections for flexible cables without end sleeve, max.	1.5 mm ² ; max. 32x 0.75 mm ² , 8x 1.5 mm ²
— Connectable cable cross-sections for flexible cables with end sleeve, min.	0.25 mm ²
— Connectable cable cross-sections for flexible cables with end sleeve, max.	1.5 mm ² ; max. 32x 0.75 mm ² , 8x 1.5 mm ²
Conductor cross-section acc. to AWG	
— Connectable cable cross-sections for massive cables, min.	24
— Connectable cable cross-sections for massive cables, max.	16; max. 32x AWG 19, 8x AWG 16
— Connectable cable cross-sections for flexible cables without end sleeve, min.	24
— Connectable cable cross-sections for flexible cables without end sleeve, max.	16; max. 32x AWG 19, 8x AWG 16
— Connectable cable cross-sections for flexible cables with end sleeve, min.	24
— Connectable cable cross-sections for flexible cables with end sleeve, max.	16; max. 32x AWG 19, 8x AWG 16
Wire end processing	
— Stripped length of cables, min.	8 mm
— Stripped length of cables, max.	11 mm
— End sleeve acc. to DIN 46228 without plastic sleeve	Form A, 10 mm long
— End sleeve acc. to DIN 46228 with plastic sleeve	Form E, 8 mm and 10 mm long
Mounting	
— Tool	Screwdriver, conical design, 3 mm to 3.5 mm
Dimensions	

Width	19.8 mm
Height	130.5 mm
Depth	43 mm
Weights	
Weight, approx.	123 g

last modified: 1/21/2021 