



OMNI-DIRECTIONAL ANTENNA FOR GSM-(2G) AND UMTS- (3G) NETWORKS, OMNIDIRECTIONAL; WEATHER RESISTANT FOR INSIDE UND OUTSIDE; 5M CONNECTION CABLE FAST CONNECTED WITH THE ANTENNA; SMA CONNECTOR; INCL. MOUNTING BRACKET, SCREWS, DOWELS

Wireless frequencies

Type of mobile wireless network / is supported / GSM	Yes
Type of mobile wireless network / is supported / UMTS	Yes
Operatng frequency	
• 850 MHz	Yes
• 900 MHz	Yes
• 1800 MHz	Yes
• 1900 MHz	Yes
• 2200 MHz	Yes

Electrical data

Radiation characteristic	omnidirectional
Antenna gain	0 dB
Standing wave ratio VSWR / maximum	2
Transmit power / maximum	20 W

Permitted ambient conditions

Ambient temperature / during operating	-40 ... +70 °C
Protection class IP	IP65

Design, dimensions and weight

Width	24 mm
Height	193 mm
Depth	24 mm

Diameter	24 mm
Net weight	310 g
Cable length / of antenna cable	5 m
Material / of outer shell	Hard PVC, UV-resistant
letzte Änderung:	May 23, 2014