


## Features

- Easy to install: fast and simple integration ensure stable performance in any application
- Waterproof, IP66 / IP68 protection
- Safe and reliable
- For use with outdoor lighting, sensor equipment, outdoor communication equipment & more



## Specification

|                                    |                                   |
|------------------------------------|-----------------------------------|
| Air Permeability                   | 180-2300 ml/min@0.07bar           |
| Membrane Material                  | ePTFE                             |
| Membrane Characteristics           | Oleophobic & Hydrophobic          |
| Body Material                      | Aluminium Alloy                   |
| Colour                             | Silver                            |
| Torque Wrench Size                 | 15                                |
| O-ring Material                    | Silica gel 60H shore hardness A   |
| Clamping Nut Material              | Aluminium Alloy                   |
| Flammability Level                 | V0                                |
| Salt Resistance                    | PH 1-14                           |
| Antibacterial Level (GB/T 2423.16) | 1 Level                           |
| Anti High & Low Temperature        | -40°C~120°C                       |
| IP Level                           | IP66 / IP68                       |
| Traceability                       | With Independent Laser Serial No. |
| Recommended Torque                 | 1.2±0.1N.m                        |
| Installation                       | Thread                            |

**Art. Nr.**  
**RND 455-01116**