

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet

Firestop®

RoHS₂
 2002/95/EC
 2011/65/UE

Halogen Free

tasker® TSK 1038 L.S.Z.H. -2x0,35 mm² DMX Digital Audio 110 Ohm Cable AES/EBU



A	B	C	D	E
---	---	---	---	---

CATEGORY Digital Audio Cable (See Audio Catalogue)

- A:** Black **L.S.Z.H.** sheath. – Flame Retardant and Halogen Free.
Outer Diam. Ø 6,30 (±0,20) mm.
- B:** Shielding O.F.C. tinned copper Braid covering 85% + O.F.C. tinned copper Drain Wire.
- C:** Waste filler between conductors and total taping in not woven polyester.
- D:** Core Insulation with PPE, colored one Red and one Blue.
Diam. Ø 1,60 mm (±0,20) mm.
- E:** O.F.C. tinned copper formation 11x0,20 mm.
Nom. Cross section 2x0,35 mm².

MARKING tasker® TSK 1038 L.S.Z.H. 2x0,35 mm² - O.F.C. Extra Flex Digital 110 Ω DMX Audio Cable – Halogen Free - Firestop® - Made In Italy

CUSTOM This product is also available in **PVC, PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	60 Ω/Km ± 5%
Capacity Core/Core	55 pF/mt
Capacity Core/Shield	62 pF/mt
Impedance	110 Ω
Max Rated Voltage	49 V
Operative Temperature	-30/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C /17.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			