


MOSA M12 FEMALE 0° FIELD-WIREABLE (IDC)4-pol., 0,14-0,34mm², shielded

Female straight


4-pole

Connection cross section: 0.14...0.34 mm²

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.

[Link to Product](#)**Illustration**

Male



Product may differ from Image

Approvals



Form

12651

Technical Data

Operating voltage	max. 50 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...0.34 mm ² (conductor diameter min. 0.1 mm)
Sealing range (cable diameter)	5.5...7.2 mm
Wire isolation	PVC, PP
Outer wire diameter	1.2...1.6 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range	-25...+85 °C
Dimensions H x W x D	49x19.5x19.5 mm

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1