

Forked clamps

With round clamping face



Version:

- Heat-treated steel
- Painted
- With round clamping face



Art. no.	26130 110
Slot width	26 mm
Length	315 mm
Suitable cheese-head screw DIN 912	M24
Clamping shoe height	40 mm
Clamping shoe width	70 mm
Diameter	38 mm
Length 2	80 mm
Length 3	56 mm
DIN	6315

EAN-Code

4020772070793