

## LED magnifying lamp TEVISIO

Waldmann **W**

### Application:

For magnifying small parts with additional light source.

### Version:

- Illuminated by LEDs
- Consumption: approx. 13 W
- IP 20 degree of protection, protection class 2
- Power supply unit, 100-240 V, 50/60 Hz, 3.4-3.6 m connection line
- Integrated membrane key for ON/OFF, dimming or visualiser function
- 3.5/8 DPT

### Advantage:

- Long service life thanks to stable and robust aluminium frame
- Optimum support in the evaluation and verification of colour and surface qualities
- Moving 2D and 3D head joint provides large action radius
- No distracting reflections thanks to clouded screen
- Lens is simple to replace



<b>Art. no.</b>	<b>41335 210</b>
<b>Model</b>	TEVISIO TVD 750/940/DM
<b>Magnification</b>	3,5-times
<b>Lens diameter</b>	160 mm
<b>Material of lens</b>	Glass
<b>Length</b>	484/500 mm
<b>Design</b>	Articulated arm with screw-on plate

### EAN-Code

401333004409 1