



Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Han® PushPull SCRJ


double ended

Hood: plastic with top entry

Cable: POF, multi mode,
980/1000 μm,
PROFINET type C

- Length: a = 1 m
a = 2 m
a = 5 m
a = 10 m
a = 20 m

- 33 53 211 0010 001
33 53 211 0020 001
33 53 211 0050 001
33 53 211 0100 001
33 53 211 0200 001



Han® PushPull SCRJ

double ended

Hood: metal with top entry

Cable: POF, multi mode,
980/1000 μm,
PROFINET type C

- Length: a = 1 m
a = 2 m
a = 5 m
a = 10 m
a = 20 m

- 33 53 211 0010 002
33 53 211 0020 002
33 53 211 0050 002
33 53 211 0100 002
33 53 211 0200 002

