FEATURES

- **Self-adhesive**

- **Quick and easy install**

- **Low flammability**

- **Clean white finish**

- **-20°C to 70°C temperature range**

- **Flexible**

RS PRO White Slotted Flexible Panel Trunking - Flexible Slot, W20 mm x D20mm, L500mm, Polypropylene

RS Stock No.: 598-608

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Polypropylene flexible trunking comes in white, giving that clean clinical finish to any work area. The adhesive flat back allows you to organise your cables without causing any permanent damage to the area it will be applied to, this also allows for simple yet effective installation. Our trunking is a round shape with low flammability, it's self-extinguishing in accordance with UL94-V1 and halogen free. The base has additional slots to accept further fixings if required making this trunking perfect for all of your cable and accessories management needs.

General Specifications

Trunking/Chain Type	Slotted Flexible Panel Trunking
Material	Polypropylene
Colour	White
Fire Behaviour	Flame Retardant, Halogen Free, Low Smoke Density, Self-extinguishing
Type of Fastening	Self-adhesive
Applications	Offices and indoor work spaces, at various lengths, Electrical workshops, Schools, Hospitals, Hotels and anywhere with customers walking amongst cables

Mechanical Specifications

Length	500mm
Width	20mm
Depth	20mm
Slot Type	Flexible

Operation Environment Specifications

Operating Temperature Range	-20°C to 70°C

Approvals

Standards Met	UL 94 V-1