

HI-765PWL

# Probe Robust HANNA

## Thermistor Probes with 1 m (3.3') cable

Thermistor probe with sharp tip for penetration of semi solid samples with 1 m (3.3') cable

All probes are pre-calibrated with a maximum error of 0.2°C ( $\pm 0.4^{\circ}\text{F}$ ). The HI 765 series can be identified by the white cap on the top of the handle, and offers a wide range of probes for measuring liquids, air & gasses, and for penetration in semisolids.

Models are available with a 1 or 10 meter cable, and colored handles for easy identification during measurements of different samples.

Order Information:

White handle

## Specifications

Accuracy	$\pm 0.2^{\circ}\text{C}$ ( $\pm 0.4^{\circ}\text{F}$ )
Cable Length	1 m (3.3')
Handle Color	White
Interchange Error	$\pm 0.2^{\circ}\text{C}$ ( $\pm 0.4^{\circ}\text{F}$ )
Probe	stainless steel AISI 316
Probe Handle	ABS
Range	-50 to 150°C (-58 to 302°F)
Response Time	8 seconds
Sensor	PTC thermistor