


FE-30-A-A-M6/2M

Fibre optics



Product characteristics

Through-beam sensor

M6

Sensing range 240 mm

Connection to fibre optic amplifiers type OIF

Range

Sensing range	OIF: 240 mm
---------------	-------------

Environment

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Design

straight

Length [mm]

2000

Min. bending radius [mm]

30, for fixed installation

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

aluminium; adapter: polyamide

Weight [kg]

0.193

Accessories

Accessories (included)

2 hexagon nuts; M6; stainless steel; 2 tooth lock washers; 1 knurled nut; M30

Remarks

Pack quantity [piece]

1