



Datenblatt - Fiche technique - Data sheet


**11.04.5652**



ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 2,0m

ROLINE Câble High Quality HD15 M/HD15 M avec noyaux de ferrite + DDC,  
2,0m

ROLINE High Quality VGA Cable + Ferrite + DDC, HD15, M/M, 2 m



Conn.1 HD15 Male Molding

Conn.2 HD15 Male Molding



Electronic Test :

1. 100% Test (Open,Short, Miss Wire)
2. Contact Resistance : 5 ohm max
3. Insulation Resistance : 10M ohm min
4. Hi-Pot : 300V DC/10ms

<b>ROTRONIC</b>		RoHS COMPLIANT	
DESCRIPTION	VGA Cable	SIZE:	A4 mm
CUSTOMER P/N	HD15M/M W/2 FERR 2M Black	UNIT.	mm
MODEL NO.		DATE.	07.04.08
NO.		SCALE.	NONE
DWG NO.		SHEET	1/1
HS CODE		REV.	1
UPC			
DRAW.	LM		
CHECK.	LH		
APP.	WENTU		

NO.	P/N	DESCRIPTION	Q'TY	UNIT
7	R87-01001	Ferrite Core 17.5*9.5*28.5	2	pcs
6	R87-04005	Copper Foil 360° Solder W=3.2cm	12/100	m
5	R90-45006	Outside Molding 45P PVC PMS:Black 3U2X	72/1000	kg
4	R91-01001	Inside Molding PE	9.5/1000	kg
3	R86-20043	Screw 40.5mm #4-40UNC Color:Black 3U2X	4	pcs
2	R71-15009	HD15P Male Solder Type Insulation Blue	2	pcs
1	61-12605	UL2919 28AWGx3Coax+24AWGx9C+AL/MY+DW+BD Jacket Color PMS:Black 3U2X OD:8.5±0.2	2	m
NO.	P/N	DESCRIPTION	Q'TY	UNIT