



Datenblatt - Fiche technique - Data sheet

21.15.0879




ROLINE S/FTP-(PiMF-)Patchkabel Kat.6a, Massivdraht, LSOH, grau, 90,0 m

Cordon ROLINE Cat.6a S/FTP (PiMF) solide LSOH, gris, 90,0 m

ROLINE S/FTP Patch Cord Cat.6a, solid, LSOH, grey, 90.0 m

1 2 3 4 5 6

Length (see below list)



Print: roline S/FTP INSTALL CABLE 23AWG 4PR ANSI/TIA 568C.2 CAT.6A LSOH XXXXXXXX-X XXXXM

Specification :

- Material :
1. RJ45 Plug :
 - 1-1. Housing : Polycarbonate, UL 94V-2, Blue color
 - 1-2. Contact finished : Min. 50 micro-inch Gold plating over min. 50 micro-inch Nickel plating on surface contact area
 - 1-3. Contact material : Phosphor Bronze
 - 1-4. Shield : Zinc Alloy with Nickel plated
 2. SR : PC 2250 UL 94V-2
 3. Cable : 23AWG Solid wire, wiring:T568B
 - 3-1. Jacket : LSOH, Gray(RAL7035)
 - 3-2. Conductor : 23 AWG Solid copper
 - 3-3. Isolation : Foam PE
 - 3-4. Shield : Aluminum Foil
 - 3-5. Cable structure : S/FTP, 4 twisted pair
 4. Minimum of the bending radius: 50mm

Item no. list:

21.15.0874	20m	21.15.0878	70m
21.15.0876	30m	21.15.0879	90m
21.15.0877	50m		

No.	MODIFIED AREA	ORIGINAL	MODIFY	DATE	MODIFIER

Item no.	21.15.0874, 21.15.0876, 21.15.0877, 21.15.0878, 21.15.0879			
Description	ROLINE Cat. 6a S/FTP Patch Cord, Solid, LSOH, grey			
*#: Matching DIM. *#: Important DIM. Others General DIM.	DRAWING	03.Jul.2014	byz	rotronic
	CHECK	03.Jul.2014	Jane	
	APPROVAL	03.Jul.2014	Frank	
GENERAL TOLERANCE OF DIMENSIONS	SCALE	DATE	NAME	
	X.XXX ±0.005 X.XX ±0.05 X.X ±0.1	1/1 (A4)	UNIT	mm
	DRAWING NO. ACBUEXX072XXXXX(SA1)			
	DRAWING CLASSIFICATION		S	SHEET 1 OF 1

1 2 3 4 5 6 10cm