

**CAB CAB PC 403018 G**



Sample photo

**Order symbol:** CAB PC 403018 G  
**Product nbr:** 8113350  
**Description:** Cabinet, PC  
**Remarks:** Latches on the long side

**EAN:** 6418074020208  
**EI. number:**  
 Finland: 3424114  
 Electric No. 8212020249  
 Denmark:  
 Electric No. Italy: 7821040  
 Electric No. Sweden: 2539971

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	400	300	180	EKIV 43 PL Mounting plate, Plastic
inch:	15.7	11.8	7.1	EKIV 27 DIN-35 Mounting rail

**Materials:**

**Material:** Polycarbonate

**Base colour:** RAL 7035 -light grey

**Cover colour:** RAL 7035 -light grey

**Gasket material:** Polyurethane

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C

**Temperature °C (continuous):** -40 ... 80 °C

**Temperature °F (short term):** -40 ... 250 °F

**Temperature °F (continuous):** -40 ... 175 °F

**Accessories:**

EKIV 43 Mounting plate

DS35270E1	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 43	Front plate
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set

**Rating:**

Ingress Protection (EN 60529): IP65

Impact Resistance (EN 62262): IK08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C: 960

**Certificates:**

Germanischer Lloyd (GL)

SGS Fimko

Lloyds Register of Shipping (LR)

Gost R

