


Non-NEMA Twist-Lock® Devices 20 Ampere, 250, 125/250 Volts and 3Ø Y 120/208 Volts AC Insulgrip® Plugs, Flanged Inlets, Connector Bodies and Receptacles




HBL9965C



HBL3325C




HBL7411C



HBL7408C

For Replacement Use Only

IP20
SUITABILITY



20A 250V
Non-NEMA
Not UL Listed



20A 125/250V
Non-NEMA
Not UL Listed

Plugs

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.360"-.930" (9-24)	HBL9965GCB	HBL9965C
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	-	HBL99CM65C

Accessories on page B-51.


Flanged Inlets

Description	Catalog Numbers
Nylon casing, back wired.	- HBL3325C

Accessories on page B-50.

For Replacement Use Only

IP20
SUITABILITY



20A 3Ø 250V AC
Non-NEMA
Not UL Listed



20A 3Ø Y 120/208V AC
Non-NEMA
Not UL Listed

Plugs

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.35"-1.15" (9-29)	HBL7411GCB	HBL7411C

Accessories on page B-53.

Flanged Inlets

Description	Catalog Numbers
Nylon casing, back wired.	- HBL7408C

Accessories on page B-52.

Notes: For technical information see page B-69.

The devices shown on this page are not listed by Underwriters Laboratories Inc. and are for replacement use only in existing installations.

CAUTION: To avoid electrical shock, review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device.