


C800X aanslagbouten (Grade 10)

360° draaibaar, 180° klapbaar en belastbaar.
Gelagerd en draait zich in juiste hijsrichting.
Volgens EN 1677-1



Type	Veilige werklast (kg)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	H (mm)	M x L (mm)	SW (mm)	Gewicht (kg/st/m)	Artikelnummer
C800X-M8x18-0.3T	300	30	13	46	38	50	105	8 x 16	30	0.48	2611108
C800X-M10x18-0.5T	500	30	13	46	38	50	105	10 x 18	30	0.48	2611110
C800X-M12x18-0.7T	700	30	13	46	38	50	105	12 x 18	30	0.50	2611112
C800X-M16x24-1.4T	1.400	30	13	46	38	50	105	16 x 20	30	0.53	2611116
C800X-M20x30-2.5T	2.500	30	13	46	38	50	105	20 x 30	30	0.53	2611120
C800X-M24x30-4.0T	4.000	30	13	46	38	50	105	24 x 30	30	0.53	2611124
C800X-M30x35-6.7T	6.700	40	18	70	58	68	153	30 x 35	58	2.85	2611130
C800X-M36x54-10T	10.000	50	23	91	90	86	200	36 x 54	80	4.62	2611136
C800X-M42x63-12.5T	12.500	50	23	91	90	86	200	42 x 63	80	5.20	2611142
C800X-M48x72-12.5T	12.500	50	23	91	90	86	200	48 x 72	80	5.20	2611148