


## SPE-158/WS - Loudspeaker



### Flush-mount full range speakers, 15 W

- Dual cone
- Slimline design with fixed metal grille



## Technical Data

Frequency range	: 100-12,000 Hz
Resonant frequency (fs)	: -
Power capability, 100 V	: -
Power capability, 8 Ohm	: 30 W <sub>MAX</sub> , 15 W <sub>RMS</sub>
Power capability, 4 Ohm	: -
SPL (1 W/m)	: 88 dB
Max. rated SPL	: -
Type of speaker	: 130
Mounting cutout	: Ø 120 mm
Mounting depth	: 34 mm
Admiss. ambient temp.	: 0-40 °C
Dimensions	: Ø 153 mm x 45 mm
Weight	: 500 g
Other features	: -