

## SylSafe EXIT Mod

SylSafe Exit-Mod EX R EM3 MT DA  
0041750



### Product features

- SylSafe Exit-Mod EX R EM3 MT DA is a recessed emergency exit sign. Comes with ISO7010 compliant legend pack. Arrows left, right, up, down and a blank sheet for single sided versions. EC legend pack is available as accessory. Viewing distance 26m. White housing colour. Maintained 3hr emergency operation with NiMH rechargeable battery. Recharge period 24 hours. Self testing with DALI monitoring capability. 4.9W, IK03, IP20. Power Factor 0.49. Class II electrical construction.



## PRODUCT OVERVIEW

Product name	SylSafe Exit-Mod EX R EM3 MT DA
Technology	LED
Type	LED
Mount	Ceiling recessed mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education, Logistics & Industry
ETIM Class	EC001957
Warranty	5 years
Fixture luminous flux (lm)	-
Electrical protection	Class II
Housing colour	White
IP rating	IP20
IK rating	IK03
Product EAN number	5410288417509

## DATA TABLE

### General data

Product name	SylSafe Exit-Mod EX R EM3 MT DA
Technology	LED
Type	LED
Mount	Ceiling recessed mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education, Logistics & Industry
ETIM Class	EC001957
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	-
Emergency duration (h)	3

### Electrical data

Mains voltage (V)	230-240V
Lamp power factor	0.49
Electrical protection	Class II

## SylSafe EXIT Mod

*SylSafe Exit-Mod EX R EM3 MT DA*

0041750

Control gear required	Yes
Drive current (mA)	60
Nominal Frequency (Hz)	50/60Hz

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK03
Nominal Product Length (mm)	300
Nominal Product Width (mm)	49
Nominal Product Height (mm)	201
Weight (kg)	0.866

### Packaging

Single packaging type	Carton
Product EAN number	5410288417509
Packaging single length / height (cm)	31.0
Packaging single width (cm)	22.6
Packaging single depth (cm)	4.4
DUN14 (outer)	05410288417509
Units per outer package	1
Packaging outer length / height (cm)	31.0
Packaging outer width (cm)	22.6
Packaging outer depth (cm)	4.4

## PHOTOMETRY

## TECHNICAL DRAWINGS

