

Nanotrack 1 - Starter track

Nanotrack Single circuit - Starter Track - 1m - White

3019010



Product features

- Nanotrack - Single circuit Starter Track, extruded aluminium body, suitable for surface mounting and suspending, Supplied with Track Unit and Live Ends, (LxWxH) 1000x30x18mm, 0.45kg, White RAL 9016, Class 1, maximum installed load: 1x3840W (1x3680W), fuse: 1x16A, supply cable: 3 x 1.5mm², 240 (230) VAC supply



PRODUCT OVERVIEW

Product name	Nanotrack Single circuit - Starter Track - 1m - White
Technology	Accessory
Mount	Track mounting
Environment	Interior
General application	Retail
ETIM Class	EC000101
E-number FI	4276773
E-number SE	7416038
E-number Norway	3208748
Warranty	5 years
Electrical protection	Class I
Housing colour	White
IP rating	IP20
Product EAN number	8711971190103

DATA TABLE

General data

Product name	Nanotrack Single circuit - Starter Track - 1m - White
Technology	Accessory
Mount	Track mounting
Environment	Interior
General application	Retail
ETIM Class	EC000101
E-number FI	4276773
E-number SE	7416038
E-number Norway	3208748
Warranty	5 years

Optical data

Adjustable chromaticity	N
-------------------------	---

Electrical data

Electrical protection	Class I
Transformer required	Yes

Nanotrack 1 - Starter track

Nanotrack Single circuit - Starter Track - 1m - White

3019010

Glow Wire Test (°C)	850
---------------------	-----

Physical data

Housing colour	White
IP rating	IP20
Weight (kg)	0.45

Packaging

Single packaging type	Carton
Product EAN number	8711971190103
Packaging single length / height (cm)	106.0
Packaging single width (cm)	4.0
Packaging single depth (cm)	4.0
Units per outer package	1
Packaging outer length / height (cm)	106.0
Packaging outer width (cm)	4.0
Packaging outer depth (cm)	4.0

TECHNICAL DRAWINGS

