

Letter marking stamp sets, font height 2 to 10 mm

Standard font, nickel-plated

ORION[®]

Application:

For labelling parts.

Execution:

- Standard lettering
- Left-engraved
- DIN 1451 typeface
- Close-spaced lettering
- Hardness at end of writing: 58-60 HRC
- Maximum strength: 1200 N/mm²
- Nickel-plated

Delivery:

In plastic box



Art. no.	56926 740
Brand	ORION
Manufacturer Part Number	56926740
Character height	4 mm
Character type provided	Letters
Number of stamps	27 PCS
Length x width x height	9 x 9 x 80 mm
Surface	Nickel plated
With depth limiter	No
Gross Weight	1.311 kg
Product Group	577

EAN

4039247316038