

Cordless combination drill and chisel hammer KH 18 LTX BL 24 Q

with Metabo quick replacement chuck

metabo®

Application:

Very light, compact cordless hammer with brushless motor for fatigue-free drilling in any working position

Execution:

- Combination drill and chisel hammer with 3 functions: Rotary hammer drilling, drilling and chiselling
- Electronic soft start for precise drilling
- LED work lamp for optimal view of the drilling site
- Maximum drilling performance, efficiency and service life thanks to brushless technology and high-performance impact mechanism
- Dust-free drilling with compact ISA 24 dust extraction
- Metabo VibraTech (MVT): non-harmful, effortless work, even in continuous use
- Metabo Quick: fast, tool-free chuck change for working with SDS-plus and straight-shank drill bits
- Vario Tacho Constamatic (VTC) full-wave electronics for working at material-compatible speeds, which remain constant under load



Art. no.	70142 154
Model	KH 18 LTX BL 24 Q
Manufacturer Article Number	601714900
Battery voltage	18 V
Battery included	No
Number of rechargeable batteries/batteries	0
Max. impact rate	4750 rpm
Max. drilling diameter in steel	13 mm
Min./max. idle speed	0-1280 rpm
Suitable for tool holding device	SDS-plus
Included in delivery	Integrated dust extraction ISA 24 replacement suction head, hammer chuck for tools with SDS-plus shanks, quick-action drill chuck for tools with cylindrical shanks, rubberised additional handle, drilling depth stop, metaBOX 185 XL, without battery pack, without charger
Sound-pressure level	88 dB
Noise level	99 dB
Max. drilling diameter in concrete	24 mm
Product Group	Prod. Gr. 745

EAN

4061792218567