

Pneumatic needle scaler RRI-4006VL

Pistol version



Application:

Suitable for longer-lasting work.

Execution:

- Ergonomic shape
- Vibration and thermally insulated handle

Advantage:

- Very high impact frequency
- For left- and right-handed use



Art. no.	75066 115
Brand	RED ROOSTER
Manufacturer Part Number	RRI-4006VL
Model	RRI-4006VL
Max. impact rate	2400 rpm
Air consumption	1.9 l/s
Number of needles with 3 mm thickness	19 PCS
Diameter of needle	3 mm
Inner hose diameter	6.5 mm
Sound-pressure level	90 dB
Weight	2.7 kg
Gross Weight	2.636 kg
Product Group	7AE

EAN

8717981183883