

## Pneumatic needle scaler RRI-4006VL

Pistol version



### Application:

Suitable for longer-lasting work.

### Version:

- Ergonomic shape
- Vibration and thermally insulated handle

### Advantage:

- Very high impact frequency
- For left- and right-handed use



|  |                  |
|--|------------------|
| <b>Art. no.</b>                              | <b>75066 115</b> |
| <b>Model</b>                                 | RRI-4006VL       |
| <b>Max. impact rate</b>                      | 2400 rpm         |
| <b>Air consumption</b>                       | 1.9 l/s          |
| <b>Number of needles with 3 mm thickness</b> | 19 PCS           |
| <b>Diameter of needle</b>                    | 3 mm             |
| <b>Inner hose diameter</b>                   | 6.5 mm           |
| <b>Sound-pressure level</b>                  | 90 dB            |
| <b>Weight</b>                                | 2.7 kg           |

### EAN-Code

8717981183883