



Model	
Product brand name	SENTRON
Product designation	accessories
Design of the product	circular conductor terminal






Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / minimum 	1.5 mm ²
<ul style="list-style-type: none"> • for copper cable / solid / maximum 	6 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum 	1.5 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / maximum 	70 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	1.5 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	70 mm ²
Wire stripping length	12,2 mm

Connections according UL	
Wire stripping length	0.5 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / maximum 	10 AWG
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	2/0 AWG

• for copper cable / finely stranded / maximum

2/0 AWG

Certificates

General Product Approval	EMC	Declaration of Conformity	other		
 CSA	 UL		 RCM	 EG-Konf.	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JD11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JD11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JD11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

09/13/2017