



PLUG-IN RELAY COMPACT UNIT AC 115V, 2 CO CONTACT LED MODULE RED SOCKET W. LOGIC ISOLATION SCREW TERMINAL

Figure similar

General technical data:		
Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• with AC		
— at 50 Hz Rated value		
— minimum	V	115
— maximum	V	115
— at 60 Hz Rated value		
— minimum	V	115
— maximum	V	115
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		2
Operating current of the auxiliary contacts		
• at AC-15		
— at 230 V	A	2.5
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable
Mechanical data:		
<b>Type of electrical connection</b>		screw-type terminals
<b>Design of the relay operating mechanism</b>		poled

Product component Plug-in socket		Yes
Width	mm	15.5
Height	mm	71
Depth	mm	77

Certificates/ approvals:

General Product Approval

other

[Declaration of Conformity](#)



### Further information

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:RT4B4S15>

**Information- and Downloadcenter (Catalogs, Brochures,...)**


<http://www.siemens.com/industrial-controls/catalogs>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:RT4B4S15>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZS:RT4B4S15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:RT4B4S15&lang=en)



last modified:

15.01.2015