



Datenblatt - Fiche technique - Data sheet

**11.04.5670**




ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 20m

ROLINE Câble écran HD15 M/M avec noyaux de ferrite + DDC, 20 m

ROLINE High Quality VGA Cable + Ferrite + DDC, HD15, M/M, 20 m


# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE



**NOTE:**

- CABLE: UL-2919 28AWG(7/0.127 T.C)\*3COAX(75 OHMS) +24AWG(7/0.20 T.C)\*9C+AL/MY+D.W+BRAID(85%) PVC JACKET, COLOR: BLACK(NK-K01) OD:  $\varnothing$  8.5 $\pm$ 0.15mm, (C2919355-1) (SPACE SHUTTLE)
- CONNECTOR:  
P1&P2:HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- ELECTRICAL TEST: <1>.100% OPEN SHORT & MIS WIRE TEST  
<2>. CONTACT RESISTANCE 3 Ohms MAX  
<3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING: <1>EACH PC / POLYBAG + BIG HEADER CARD + BAR CODE LABEL.  
<2>EACH PC / POLYBAG + BAR CODE LABEL.



DWG	P/N	LFT(mm)	BAR CODE NO.	PACKING	CTN BAR CODE
120-3272-3	11.04.5670	20000 $\pm$ 200	7611990192267	<2>	7611990992263
120-3272-2	11.04.5660	10000 $\pm$ 100	7611990192250	<2>	7611990992256
120-3272-1	11.04.5653	3000 $\pm$ 30	7611990192243	<1>	7611990992249

Tolerance Inch		M/M	
.X	.015	.30	
.XX	.010	.10	
.XXX	.005	.05	

Drawn	FANNIE 09/24/10'
Check	
Engr	

App'd	Customer	T-RAG
Scale	NONE	Units
Dwg No.	120-3272	REV: A
Sheet	1/1	

**Rotronic co., LTD.**

HDB15/M-HDB15/M W/FERRITE CORES CABLE