

## Han M23 P HBMA-rotatable 25x25 2,7mm



Part number	09 15 600 0902
Specification	Han M23 P HBMA-rotatable 25x25 2,7mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09156000902">https://b2b.harting.com/09156000902</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® M23 Power
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Angled Rotatable

### Version

Size	M23
Fixing	Fixing hole 4 x 2.75 mm

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black

### Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

### Commercial data

Packaging size	5
Net weight	74.2 g
Country of origin	Germany



Pushing Performance

## Commercial data

Customs tariff number	85366990
-----------------------	----------

---