



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKS
Associated body	ZCKS5 ZCKSD35 ZCKS9H29 ZCKSD39H29 ZCKSD37 ZCKS1H29 ZCKSD37H29 ZCKS7H29 ZCKS6 ZCKS9 ZCKSD31H29 ZCKS5H29 ZCKS2 ZCKS1 ZCKSD39 ZCKS7 ZCKS8 ZCKS2H29 ZCKSD35H29 ZCKSD31 ZCKS6H29 ZCKS8H29
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	00785901102878
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	No
Country of origin	ID

Packing Units

Package 1 Height	0.330 dm
Package 1 width	0.630 dm
Package 1 Length	0.750 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------