

## Die, HSS PG right, pre-slotted and 1.75 thread chamfer

For universal use up to 700 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For tapping male armoured pipe threads in the steel, stainless steel, NF metals and special alloy material groups up to a strength of 700 N/mm<sup>2</sup>.

### Execution:

- Right-handed die with spiral point, pre-slotted, 1.75-threaded chamfer

### Advantage:

- Innovative cutting geometry for high process reliability



<b>Art. no.</b>	<b>13491 090</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	1349 1090
<b>Thread type</b>	PG
<b>Cutting material</b>	HSS
<b>Thread type x nominal diameter in inches</b>	PG 9 in
<b>Number of thread starts per inch</b>	18
<b>Outer diameter</b>	38 mm
<b>Height</b>	10 mm
<b>Cutting direction</b>	Right-hand cutting
<b>DIN</b>	40434
<b>Gross Weight</b>	0.137 kg
<b>Product Group</b>	1DC

### EAN

403924707489 1