

copy and face milling heads M100™
for indexable milling inserts RD.. 1606..



Application:

universal face and copy milling.

Execution:

- robust and rigid milling cutter body, suitable for the most demanding machining tasks
- indexable inserts with twist lock for optimum safety
- with internal cooling



Art. no.	16042 302
Brand	WIDIA
Manufacturer Part Number	2021359
Max. cutting edge diameter	52 mm
Length	40 mm
Bore diameter	22 mm
max. ap	8 mm
Number of cutting edges	4 PCS
Gross Weight	0.200 kg
Product Group	1XJ

EAN

4021169171413