

Precision pointer micrometer



Application

For quick testing of parts from series production.

Execution

- Adjustable tolerance marks
- Carbide measuring faces
- Movable measuring probe for lifting the anvil

Delivery

In a case

Art. No.	31471 125
Calibration Group	AN
Min./max. length measuring range	25-50 mm
Indicating calliper measuring range	+/- 0,065 mm
Digit increment, micrometer	0.01 mm
Digit increment, indicating calliper	0.001 mm
Indicating calliper error limit	0.001 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Measurement force	9 N
Measuring surface diameter	7.5 mm
DIN	863

EAN-Code

405029339675 1